

Ordering Vapor Proof Lenses from PARS is easy



1. Measure length, width & depth of your old lens
2. Specify: Rolled Flange OR Straight Flange
3. Tell us how many units you need.
4. Provide contact information
5. Email or fax your request to PARS Lighting.

Quantity:

Length: to 1/16"..... Width to 1/16".....Depth to 1/16'.....'

Flange: Rolled or Straight

Finishes: Clear | Ribbed

Please supply sample for proper fit

Call our office for assistance. We are here to serve you.

| | |
|------------------|--|
| Contact Name: | |
| Company: | |
| Phone: | |
| Fax: | |
| Address: | |
| City, State, Zip | |
| Comments: | |